- 1. WALL/KILN SPACING: 12" [30.5cm] SPACING BETWEEN SIDES OF KILN AND WALLS 4. OR OTHER OBJECTS. 18" [45.7cm] IS RECOMMENDED. LEAVE AT LEAST 18" [45.7cm] BETWEEN TWO KILNS.
- 2. AMBIENT VENTILATION: SEE CHART TO RIGHT FOR RATINGS. TO CALCULATE REQUIREMENTS, SEE hotkilns.com/calculate-kiln-room-ventilation.
- 3. KILN VENTILATION: L&L VENT-SURE KILN VENT RECOMMENDED FOR SAFETY AND LONGER ELEMENT LIFE. OPTIONAL CONTROL ALLOWS VENT TO BE TURNED ON AND OFF WITH CONTROL.


OTHER INFO: REFER TO INSTALLATION INSTRUCTIONS AND CAUTIONS INSTRUCTIONS FOR OTHER REQUIREMENTS AND SAFETY INFORMATION, REFER TO WIRING DIAGRAM FOR ELECTRICAL HOOKUP INFORMATION.

5. MAX LOAD WEIGHT: SEE hotkilns.com/load-weight.

WEIGHT OF KILN: 365 LBS, 166 KG

ROOM VENTILATION (THIS IS IN ADDITION TO KILN VENTING):			
AT TEMP F	BTUS	AT TEMP C	KILOJOULES
1800F	12173	980C	12844
2000F	14232	1095C	15016
2232F	16806	1222C	17731
2350F	18190	1285C	19192

BTIIS/ KII O IOIII ES PER HOUR NEEDED TO BE VENTED WITH AMBIENT



02/01/20 DSL JD2918-3 (3" BRICK) GENERAL DIMENSIONS 3

NEW

5

1/3 0

235-000-60-2

